


Specification Guide

HD Series A1 Refrigerants

Premier Horizontal Evaporator Coils

with Side Connections



Contents	Page
Nomenclature.....	2
Dimensions	3
Airflow Data.....	4



Product improvement is a continuous process at Advanced Distributor Products. Therefore, product specifications are subject to change without notice and without obligation on our part. Please contact your ADP representative or distributor to verify details.

© 2025 by Advanced Distributor Products. All rights reserved.

Product Features

- Rifled copper tubing.
- Lanced fin design.
- Dual 3/4" FPT condensate drains on front of coil.
- Refrigerant connections are 3/8" ODF liquid and 7/8" ODF suction.
- Non-captive panels allow access to inside of cabinet without the need to cut refrigerant lines.
- Optional painted or embossed galvanized steel cabinets.
- Side panel with only six screws for fast and easy coil access.
- UV resistant drain pans are molded of high temperature (450 deg. F) engineered polymer.
- Coils are air pressure tested at 500 psi, leak tested with Helium, sealed with rubber plugs and then charged with dry air.
- "No-hassle" 5-year warranty. 10 year Limited Warranty available.
- Threaded expansion valves available factory installed or as a field installed kit.
- Heavy 24 gauge embossed galvanized cabinets fully lined with 5/8" foil faced insulation.
- All coils are foam packed and include bar coding on label.
- Easy to use filler strip, if coil dimensions are larger than furnace.
- Drain pan has trough to fully drain condensate away.
- Microban® antimicrobial additive to inhibit the growth of mold and mildew in the drain pan.

Nomenclature

H	D02	1	24	E	145	B	21	47	AP																		
Cabinet Color H = Embossed A = Armstrong C = Carrier / Bryant / Payne G = ICP J = Goodman / Amana N = Nordyne R = Rheem / Ruud T = Trane / American Standard Y = York / Luxaire / Coleman Slab Number D = Copper slab P = Aluminum slab Metering Device 1 = Piston (R-410A) ^[1] 7 = Bleed HP TXV (R-410A) 9 = Non-bleed HP TXV (R-410A) Nominal MBTUH Cabinet Width E = 21.5" (standard) Cabinet Height 145 = 14.5" 175 = 17.5" 210 = 21.0" 245 = 24.5" Product Code 47 = Refrigerant connections on side of cabinet Cabinet Length 21 = 21.5" 26 = 26.5" 31 = 31.5" Duct Flange B = 0.75" (standard) AP = TXV access port ^[1] Installed Piston Sizes <table border="1"> <thead> <tr> <th>MBTUH</th> <th>R-410A</th> </tr> </thead> <tbody> <tr><td>12</td><td>41</td></tr> <tr><td>18</td><td>49</td></tr> <tr><td>24</td><td>53</td></tr> <tr><td>30</td><td>59</td></tr> <tr><td>36</td><td>67</td></tr> <tr><td>42</td><td>73</td></tr> <tr><td>48</td><td>76</td></tr> <tr><td>60</td><td>93</td></tr> </tbody> </table>										MBTUH	R-410A	12	41	18	49	24	53	30	59	36	67	42	73	48	76	60	93
MBTUH	R-410A																										
12	41																										
18	49																										
24	53																										
30	59																										
36	67																										
42	73																										
48	76																										
60	93																										

Note: Cabinet length not a selectable option, see cased dimensions.

[1] Piston will always be sized to match the nominal MBTUH rating of the coil.

"Core" options are preferred and will have better pricing and availability versus "Non-Core" options.

Dimensions


	Slab * Number	Nominal Tonnage	Dimensions (in)		Pallet Qty	Weight (lbs)	
			Height	Length		CU	AL
Core Slabs	(D,P) 12	2.0 - 3.0	14.5	26.5	8	50	40
	(D,P) 13	2.5 - 3.5	17.5	21.5	8	50	40
	(D,P) 14	2.5 - 4.0	17.5	26.5	8	50	40
	(D,P) 15	3.0 - 4.0	17.5	26.5	8	56	45
	(D,P) 16	3.0 - 5.0	21	26.5	4	61	49
	(D,P) 17	3.5 - 5.0	21	26.5	4	64	52
	(D,P) 19	3.5 - 5.0	21	26.5	4	60	48
	(D,P) 21	1.5 - 3.0	14.5	31.5	4	55	43
	(D,P) 29	3.5 - 5.0	21	31.5	2	64	52
	(D,P) 38	3.0 - 4.0	17.5	31.5	4	56	45
	(D,P) 42	1.5 - 3.0	14.5	26.5	8	50	40
	(D,P) 44	1.5 - 3.0	14.5	31.5	4	58	47
	(D,P) 45	2.5 - 3.5	17.5	26.5	8	56	45
	(D,P) 52	3.5 - 5.0	21	31.5	2	63	51
	(D,P) 74	3.0 - 4.0	21	21.5	4	50	40
	(D,P) 75	3.0 - 4.0	21	21.5	4	50	40
	(D,P) 78	2.0 - 4.0	17.5	31.5	4	70	56
Non-Core Slabs	(D,P) 03	2.0 - 3.0	14.5	26.5	8	49	40
	(D,P) 04	2.5 - 3.5	17.5	21.5	8	45	36
	(D,P) 05	2.5 - 4.0	17.5	26.5	8	47	38
	(D,P) 06	3.0 - 4.0	17.5	26.5	8	50	40
	(D,P) 07	3.0 - 5.0	21	26.5	4	51	41
	(D,P) 11	1.5 - 2.5	14.5	21.5	8	50	40
	(D,P) 18	3.0 - 5.0	24.5	26.5	4	58	47
	(D,P) 26	2.0 - 4.0	17.5	31.5	4	53	43
	(D,P) 27	3.0 - 5.0	21	31.5	2	63	51
	(D,P) 47	3.0 - 4.0	21	26.5	4	60	48
	(D,P) 50	3.5 - 5.0	21	31.5	2	63	51
	(D,P) 57	3.5 - 4.0	21	31.5	2	63	51
	(D,P) 72	2.0 - 3.0	17.5	21.5	8	53	43
	(D,P) 76	4.0 - 5.0	24.5	21.5	4	64	52
	(D,P) 77	4.0 - 5.0	24.5	26.5	4	74	60
	(D,P) 79	3.5 - 5.0	24.5	26.5	4	75	60

* D = Copper slab; P = Aluminum slab

Opening Type	Opening Dimensions by Cabinet Height			
	14.5"	17.5"	21"	24.5"
Supply opening (Height x Width)	13" x 19.75"	16" x 19.75"	19.5" x 19.75"	23" x 19.75"
Return opening (Height x Width)	13.5" x 20.25"	16.5" x 20.25"	20" x 20.25"	23.5" x 20.25"

Refrigerant Connections
Liquid Line - 3/8" ODF
Suction Line - 7/8" ODF

Drain Connections
3/4" FPT



Airflow Data

	Slab Number	Nominal Tonnage	^ Air Pressure Drop (in WC) by CFM							
			600	800	1000	1200	1400	1600	1800	2000
Core Slabs	(D,P) 12	1.5 - 3.0	0.11	0.17	0.25	0.35	-	-	-	-
	(D,P) 13	1.5 - 3.5	0.08	0.14	0.20	0.27	0.36	-	-	-
	(D,P) 14	2.5 - 4.0	-	-	0.17	0.24	0.32	0.41	-	-
	(D,P) 15	3.0 - 4.0	-	-	0.14	0.20	0.28	0.35	-	-
	(D,P) 16	3.0 - 5.0	-	-	-	0.17	0.23	0.29	0.36	0.43
	(D,P) 17	3.0 - 5.0	-	-	0.10	0.14	0.19	0.24	0.25	0.36
	(D,P) 19	3.5 - 5.0	-	-	-	-	0.22	0.33	0.41	0.48
	(D,P) 21	1.5 - 3.0	0.09	0.13	0.20	0.27	-	-	-	-
	(D,P) 29	3.5 - 5.0	-	-	-	-	0.12	0.15	0.19	0.23
	(D,P) 38	3.0 - 4.0	-	-	-	0.18	0.25	0.31	-	-
	(D,P) 42	1.5 - 3.0	0.09	0.14	0.20	0.28	-	-	-	-
	(D,P) 44	1.5 - 3.0	0.06	0.10	0.14	0.20	-	-	-	-
	(D,P) 45	2.5 - 3.5	-	-	0.19	0.27	0.35	-	-	-
	(D,P) 52	3.5 - 5.0	-	-	0.12	0.16	0.20	0.26	0.32	0.39
	(D,P) 74	3.0 - 4.0	-	-	0.19	0.25	0.33	0.41	-	-
Non-Core Slabs	(D,P) 75	3.0 - 5.0	-	-	-	0.20	0.26	0.33	-	-
	(D,P) 78	2.0 - 4.0	-	0.09	0.12	0.17	0.23	0.30	-	-
	(D,P) 03	2.0 - 3.0	-	0.16	0.25	0.35	-	-	-	-
	(D,P) 04	2.5 - 3.5	-	-	0.17	0.23	0.34	-	-	-
	(D,P) 05	2.5 - 4.0	-	-	0.13	0.19	0.25	0.32	-	-
	(D,P) 06	2.5 - 4.0	-	0.09	0.13	0.18	0.24	0.27	-	-
	(D,P) 07	3.0 - 5.0	-	-	-	0.14	0.19	0.24	0.30	0.35
	(D,P) 11	1.5 - 2.5	0.15	0.25	0.37	-	-	-	-	-
	(D,P) 18	3.0 - 5.0	-	-	-	0.11	0.14	0.18	0.23	0.28
	(D,P) 26	2.0 - 4.0	-	0.08	0.11	0.16	0.21	0.27	-	-
	(D,P) 27	3.0 - 5.0	-	-	-	0.11	0.15	0.18	0.23	0.28
	(D,P) 47	2.0 - 3.0	-	0.11	0.16	0.17	-	-	-	-
	(D,P) 50	3.5 - 5.0	-	-	-	-	0.16	0.21	0.27	0.33
	(D,P) 57	3.0 - 4.0	-	-	-	0.14	0.18	0.22	-	-
	(D,P) 72	2.0 - 3.0	-	0.19	0.27	0.37	-	-	-	-
	(D,P) 76	3.0 - 5.0	-	-	-	0.17	0.22	0.28	0.34	0.40
	(D,P) 77	3.5 - 5.0	-	-	0.11	0.14	0.19	0.21	0.27	0.34
	(D,P) 79	3.5 - 5.0	-	-	-	-	0.22	0.28	0.34	0.40

* D = Copper slab; P = Aluminum slab

^ Air pressure drop data is under dry coil conditions. For wet coil conversion at standard AHRI conditions, use 1.3 multiplier.

