


# Specification Guide

## V Series

### Premier Horizontal Evaporator Coils

with Top Connections



<b>Contents</b>	<b>Page</b>
Product Features .....	2
Nomenclature.....	2
Dimensions .....	3
Airflow Data.....	4



Product improvement is a continuous process at Advanced Distributor Products. Therefore, product specifications are subject to change without notice and without obligation on our part. Please contact your ADP representative or distributor to verify details.

© by **Advanced Distributor Products**. All rights reserved.

# Product Features

- High efficiency lanced fin design.
- “No-hassle” 5 year warranty.
- R-22, R-410A, AC & Heat Pump compatible.
- All coils have durable packaging with bar coded labels on the box.
- Threaded expansion valves available factory installed or as a field installed kit.
- Coils are air pressure tested at 500 psi, leak tested with helium, sealed with rubber plugs, then charged with dry air.
- Piston options include externally accessible body for easy piston change out and/or TXV installation.
- Microban® antimicrobial additive to inhibit the growth of mold and mildew in the drain pan.
- UV resistant drain pans are molded of high temperature (450 deg. F) engineered polymer.
- Dual 3/4" FPT condensate drains on front-left and front-right side of drain pans.
- Patented HydroTEC™ low water retention drain pan.
- Copper refrigerant connections for easy brazing on both copper and aluminum slab models.
- Intertek lab tested 1% or less cabinet air leakage for better efficiency.
- Cased coil cabinets are fully lined with 5/8" foil faced insulation.
- Optional painted or embossed galvanized steel cabinets.
- Short cabinet with easy access.
- Non-captive refrigerant lines with long stubs make for easy installation.
- Enhanced refrigerant pipe grommets: secure, tight, and easy to install.
- Copper distributor tube assembly provides brass to brass threads for trouble-free service of TXV.
- Expansion valve with improved temperature sensing:
  1. Mounted inside cabinet to prevent external sweating
  2. Bulb clamped standard factory installed
- Easy to use filler strip, for use if coil dimensions are larger than furnace.
- Easy to remove access panel with only 4 screws.
- Refrigerant connections on top of coil.
- Piston models standard with TXV access port.
- Dedicated cutouts for condensate drains reduce air leakage.
- Refrigerant connections in center of coil.
- Drain pan has trough to fully drain condensate away.
- TXV bulbs come standard attached to header assembly.

# Nomenclature

	<b>V</b>	<b>24</b>	<b>H</b>	<b>145</b>	<b>D03</b>	<b>6</b>																															
<p><b>Cabinet Color</b></p> <p><b>V</b> = Embossed  <b>A</b> = Armstrong  <b>C</b> = Carrier / Bryant / Payne  <b>D</b> = Ducane / Aire-Flo  <b>G</b> = ICP  <b>J</b> = Goodman / Amana  <b>L</b> = Lennox  <b>N</b> = Nordyne  <b>R</b> = Rheem / Ruud  <b>T</b> = Trane / American Standard  <b>Y</b> = York / Luxaire / Coleman</p> <p><b>Nominal MBTUH</b></p> <p><b>Coil Type</b>  <b>H</b> = Horizontal A-Coil</p> <p><b>Cabinet Height</b></p> <p><b>140</b> = 14.00" (Rheem / Ruud)  <b>142</b> = 14.25" (Carrier / Bryant / Payne)  <b>145</b> = 14.50"  <b>175</b> = 17.50"  <b>210</b> = 21.00"  <b>245</b> = 24.50"  <b>252</b> = 25.25"</p>							<p><b>Metering Device</b></p> <p><b>1</b> = Piston (R-410A)*  <b>2</b> = Piston (R-22)*  <b>6</b> = Non-Bleed A/C TXV (R-410A)  <b>7</b> = Bleed HP-A/C TXV (R-410A)**  <b>8</b> = Bleed A/C TXV (R-410A)**  <b>9</b> = Non-Bleed HP-A/C TXV (R-410A)  <i>** 7 and 8 valve options available only for York family products.</i></p> <p><b>Slab Number</b></p> <p><b>D</b> = Copper slab  <b>P</b> = Aluminum slab</p>																														
							<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3">Installed Piston Sizes</th> </tr> <tr> <th>MBTUH</th> <th>R-22</th> <th>R-410A</th> </tr> </thead> <tbody> <tr><td>12</td><td>41</td><td>41</td></tr> <tr><td>18</td><td>53</td><td>49</td></tr> <tr><td>24</td><td>59</td><td>53</td></tr> <tr><td>30</td><td>67</td><td>59</td></tr> <tr><td>36</td><td>73</td><td>67</td></tr> <tr><td>42</td><td>80</td><td>73</td></tr> <tr><td>48</td><td>84</td><td>76</td></tr> <tr><td>60</td><td>93</td><td>93</td></tr> </tbody> </table> <p><i>* Piston will always be sized to match the nominal BTU rating of the coil.</i></p>	Installed Piston Sizes			MBTUH	R-22	R-410A	12	41	41	18	53	49	24	59	53	30	67	59	36	73	67	42	80	73	48	84	76	60	93	93
Installed Piston Sizes																																					
MBTUH	R-22	R-410A																																			
12	41	41																																			
18	53	49																																			
24	59	53																																			
30	67	59																																			
36	73	67																																			
42	80	73																																			
48	84	76																																			
60	93	93																																			

# Dimensions

Slab * Number	Nominal Tonnage	Dimensions (in)		Pallet Qty	Weight (lbs)	
		Height	Length		CU	AL
(D,P) 02	2.0 - 3.0	14/14.25/14.5	21.5	16	47	38
(D,P) 03	2.0 - 3.0	14/14.25/14.5	26.5	8	49	40
(D,P) 04	2.5 - 3.5	17.5	21.5	16	45	36
(D,P) 05	2.5 - 4.0	17.5	26.5	4	47	38
(D,P) 06	3.0 - 4.0	17.5	26.5	4	50	40
(D,P) 07	3.0 - 5.0	21	26.5	6	51	41
(D,P) 08	3.5 - 5.0	21	26.5	6	80	64
(D,P) 09	3.5 - 5.0	24.5	26.5	2	87	70
(D,P) 11	1.5 - 2.5	14/14.25/14.5	21.5	16	50	40
(D,P) 12	2.0 - 3.0	14/14.25/14.5	26.5	8	50	40
(D,P) 13	2.5 - 3.5	17.5	21.5	16	50	40
(D,P) 14	2.5 - 4.0	17.5	26.5	4	50	40
(D,P) 15	3.0 - 4.0	17.5	26.5	4	56	45
(D,P) 16	3.0 - 5.0	21	26.5	6	61	49
(D,P) 17	3.5 - 5.0	21	26.5	6	64	52
(D,P) 18	3.0 - 5.0	24.5	26.5	2	58	47
(D,P) 19	3.5 - 5.0	21	26.5	6	60	48
(D,P) 20	3.5 - 5.0	24.5	26.5	2	60	48
(D,P) 21	1.5 - 3.0	14/14.25/14.5	31.5	8	55	43
(D,P) 22	1.5 - 3.0	14/14.25/14.5	36.5	8	57	48
(D,P) 25	2.5 - 3.0	17.5	26.5	4	50	40
(D,P) 26	2.0 - 4.0	17.5	31.5	4	53	43
(D,P) 27	3.0 - 5.0	21	31.5	4	63	51
(D,P) 28	2.5 - 3.0	21	26.5	6	62	50
(D,P) 29	3.5 - 5.0	21	31.5	4	64	52
(D,P) 30	3.5 - 5.0	21	36.5	6	80	64
(D,P) 36	3.0 - 4.0	17.5	26.5	4	55	44
(D,P) 38	3.0 - 4.0	17.5	31.5	4	56	45
(D,P) 42	1.5 - 3.0	14/14.25/14.5	26.5	8	50	40
(D,P) 43	1.5 - 3.0	14/14.25/14.5	36.5	8	60	48
(D,P) 44	1.5 - 3.0	14/14.25/14.5	31.5	8	58	47
(D,P) 45	2.5 - 3.5	17.5	26.5	4	56	45
(D,P) 46	2.0 - 4.0	17.5	36.5	4	63	51
(D,P) 47	3.0 - 4.0	21	26.5	6	60	48
(D,P) 48	2.0 - 3.0	24.5	26.5	2	60	48
(D,P) 49	4.0 - 5.0	24.5	26.5	2	87	70



Slab * Number	Nominal Tonnage	Dimensions (in)		Pallet Qty	Weight (lbs)	
		Height	Length		CU	AL
(D,P) 50	3.5 - 5.0	21	31.5	4	63	51
(D,P) 51	3.5 - 5.0	24.5	31.5	4	63	51
(D,P) 52	3.5 - 5.0	21	31.5	4	63	51
(D,P) 53	3.5 - 5.0	24.5	31.5	4	63	51
(D,P) 54	3.5 - 5.0	25.25	31.5	4	75	60
(D,P) 55	1.5 - 3.0	14/14.25/14.5	31.5	8	59	48
(D,P) 56	4.0 - 5.0	24.5	36.5	2	75	60
(D,P) 57	3.5 - 4.0	21	31.5	4	63	51
(D,P) 58	3.5 - 5.0	24.5	26.5	2	58	47
(D,P) 59	3.5 - 5.0	24.5	31.5	4	60	48
(D,P) 62	2.0 - 2.5	17.5	21.5	16	47	38
(D,P) 63	2.0 - 3.0	17.5	21.5	16	48	39
(D,P) 64	2.5 - 3.5	21	21.5	12	45	36
(D,P) 65	3.0 - 4.0	21	21.5	12	45	36
(D,P) 66	3.0 - 4.0	21	21.5	12	64	52
(D,P) 67	3.0 - 5.0	24.5	21.5	4	67	54
(D,P) 68	3.5 - 5.0	24.5	26.5	2	73	59
(D,P) 71	2.0 - 2.5	17.5	21.5	16	50	40
(D,P) 72	2.0 - 3.0	17.5	21.5	16	53	43
(D,P) 73	2.5 - 3.5	21	21.5	12	50	40
(D,P) 74	3.0 - 4.0	21	21.5	12	50	40
(D,P) 75	3.0 - 4.0	21	21.5	12	50	40
(D,P) 76	4.0 - 5.0	24.5	21.5	4	64	52
(D,P) 77	4.0 - 5.0	24.5	26.5	2	74	60
(D,P) 78	2.0 - 4.0	17.5	31.5	4	70	56
(D,P) 79	3.5 - 5.0	24.5	26.5	2	75	60
(D,P) 87	2.0 - 3.0	24.5	26.5	2	70	56
(D,P) 88	2.5 - 3.0	21	21.5	12	56	45
(D,P) 89	2.5 - 3.0	21	21.5	12	56	45

\* D = Copper slab; P = Aluminum slab

Cabinet Height (in)	14	14.25	14.5	17.5	21	24.5	25.25
Supply opening H x W	12.5 x 19.5	12.75 x 19.5	13 x 19.5	16 x 19.5	19.5 x 19.5	23 x 19.5	23.75 x 19.5
Return opening H x W	13 x 20	13.25 x 20	13.5 x 20	16.5 x 20	20 x 20	23.5 x 20	24.25 x 20

Refrigerant Connections
Liquid Line - 3/8" ODF
Suction Line - 7/8" ODF

Drain Connections - 3/4" FPT Condensate drain connections on both the front and back sides of cabinet.



# Airflow Data

Slab * Number	Nominal Tonnage	^ Air Pressure Drop (in WC) by CFM							
		600	800	1000	1200	1400	1600	1800	2000
(D,P) 02	1.5 - 2.5	0.17	0.27	0.40	-	-	-	-	-
(D,P) 03	2.0 - 3.0	-	0.16	0.25	0.35	-	-	-	-
(D,P) 04	2.5 - 3.5	-	-	0.17	0.23	0.34	-	-	-
(D,P) 05	2.5 - 4.0	-	-	0.13	0.19	0.25	0.32	-	-
(D,P) 06	2.5 - 4.0	-	0.09	0.13	0.18	0.24	0.27	-	-
(D,P) 07	3.0 - 5.0	-	-	-	0.14	0.19	0.24	0.30	0.35
(D,P) 08	3.5 - 5.0	-	-	-	0.13	0.17	0.21	0.27	0.32
(D,P) 09	3.5 - 5.0	-	-	-	-	0.15	0.18	0.23	0.27
(D,P) 11	1.5 - 2.5	0.15	0.25	0.37	-	-	-	-	-
(D,P) 12	1.5 - 3.0	0.11	0.17	0.25	0.35	-	-	-	-
(D,P) 13	1.5 - 3.5	0.08	0.14	0.20	0.27	0.36	-	-	-
(D,P) 14	2.5 - 4.0	-	-	0.17	0.24	0.32	0.41	-	-
(D,P) 15	3.0 - 4.0	-	-	0.14	0.20	0.28	0.35	-	-
(D,P) 16	3.0 - 5.0	-	-	-	0.17	0.23	0.29	0.36	0.43
(D,P) 17	3.0 - 5.0	-	-	0.10	0.14	0.19	0.24	0.25	0.36
(D,P) 18	3.0 - 5.0	-	-	-	0.11	0.14	0.18	0.23	0.28
(D,P) 19	3.5 - 5.0	-	-	-	-	0.22	0.33	0.41	0.48
(D,P) 20	3.5 - 5.0	-	-	-	-	0.19	0.24	0.29	0.34
(D,P) 21	1.5 - 3.0	0.09	0.13	0.20	0.27	-	-	-	-
(D,P) 22	1.5 - 3.0	0.06	0.09	0.13	0.18	-	-	-	-
(D,P) 25	2.5 - 3.0	-	-	0.15	0.21	-	-	-	-
(D,P) 26	2.0 - 4.0	-	0.08	0.11	0.16	0.21	0.27	-	-
(D,P) 27	3.0 - 5.0	-	-	-	0.11	0.15	0.18	0.23	0.28
(D,P) 28	2.5 - 3.0	-	-	-	0.14	0.19	0.23	0.29	0.35
(D,P) 29	3.5 - 5.0	-	-	-	-	0.12	0.15	0.19	0.23
(D,P) 30	3.5 - 5.0	-	-	-	-	0.15	0.19	0.24	0.29
(D,P) 36	3.0 - 4.0	-	-	-	0.20	0.27	0.33	-	-
(D,P) 38	3.0 - 4.0	-	-	-	0.18	0.25	0.31	-	-
(D,P) 42	1.5 - 3.0	0.09	0.14	0.20	0.28	-	-	-	-
(D,P) 43	1.5 - 3.0	0.07	0.12	0.17	0.24	-	-	-	-
(D,P) 44	1.5 - 3.0	0.06	0.10	0.14	0.20	-	-	-	-
(D,P) 45	2.5 - 3.5	-	-	0.19	0.27	0.35	-	-	-
(D,P) 46	2.0 - 4.0	-	0.05	0.08	0.11	0.15	0.19	-	-
(D,P) 47	2.0 - 3.0	-	0.11	0.16	0.17	-	-	-	-
(D,P) 48	2.0 - 3.0	-	0.09	0.14	0.19	-	-	-	-
(D,P) 49	4.0 - 5.0	-	-	-	-	0.16	0.20	0.25	0.30
(D,P) 50	3.5 - 5.0	-	-	-	-	0.16	0.21	0.27	0.33
(D,P) 51	3.5 - 5.0	-	-	-	-	0.12	0.15	0.19	0.23
(D,P) 52	3.5 - 5.0	-	-	0.12	0.16	0.20	0.26	0.32	0.39
(D,P) 53	3.5 - 5.0	-	-	-	-	0.17	0.22	0.27	0.33
(D,P) 54	3.5 - 5.0	-	-	-	-	0.16	0.20	0.25	0.30
(D,P) 55	1.5 - 3.0	0.09	0.15	0.21	0.30	-	-	-	-
(D,P) 56	4.0 - 5.0	-	-	-	-	0.13	0.16	0.21	0.25
(D,P) 57	3.0 - 4.0	-	-	-	0.14	0.18	0.22	-	-
(D,P) 58	3.5 - 5.0	-	-	-	-	0.17	0.22	0.28	0.33
(D,P) 59	3.5 - 5.0	-	-	-	-	0.18	0.23	0.29	0.34
(D,P) 62	1.5 - 2.5	0.13	0.22	0.32	-	-	-	-	-
(D,P) 63	2.0 - 3.0	-	0.17	0.24	0.33	-	-	-	-
(D,P) 64	2.5 - 3.5	-	-	0.19	0.26	0.34	-	-	-
(D,P) 65	2.5 - 4.0	-	-	0.17	0.23	0.30	-	-	-
(D,P) 66	3.0 - 4.0	-	-	-	0.18	0.24	0.30	-	-
(D,P) 67	3.0 - 5.0	-	-	-	0.16	0.20	0.25	0.31	0.37
(D,P) 68	3.5 - 5.0	-	-	-	-	0.15	0.19	0.23	0.27
(D,P) 71	1.5 - 2.5	0.15	0.24	0.35	-	-	-	-	-
(D,P) 72	2.0 - 3.0	-	0.19	0.27	0.37	-	-	-	-
(D,P) 73	2.5 - 4.0	-	-	0.21	0.29	0.37	-	-	-
(D,P) 74	3.0 - 4.0	-	-	0.19	0.25	0.33	0.41	-	-
(D,P) 75	3.0 - 5.0	-	-	-	0.20	0.26	0.33	-	-
(D,P) 76	3.0 - 5.0	-	-	-	0.17	0.22	0.28	0.34	0.40
(D,P) 77	3.5 - 5.0	-	-	0.11	0.14	0.19	0.21	0.27	0.34
(D,P) 78	2.0 - 4.0	-	0.09	0.12	0.17	0.23	0.30	-	-
(D,P) 79	3.5 - 5.0	-	-	-	-	0.22	0.28	0.34	0.40
(D,P) 87	2.0 - 3.0	-	0.09	0.13	0.17	-	-	-	-
(D,P) 88	2.5 - 3.0	-	-	0.21	0.29	-	-	-	-
(D,P) 89	2.5 - 3.0	-	-	0.13	0.18	-	-	-	-

\* D = Copper slab; P = Aluminum slab

^ Air pressure drop data is under dry coil conditions. For wet coil conversion at standard AHRI conditions, use 1.3 multiplier.